



WE253T

TV+FM twin direct Essensya Titane

Technical properties

Architecture

Type TV+FM

Configuration

Antibacterial treatment No

Connectivity

Passband 4 - 862 MHz

Dimensions

Depth of installed product 11 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 75x75x32

Width of installed product 75 mm

Attenuation

Tap loss at 860 MHz 1 dB

Capacity

Number of modules for WA 2

Materials

Colour white

Installation, mounting

Mounting type various

Connection

Type of connection with screw

Equipment

Number of outputs 2

Safety

IK protection code against mechanical impacts 01

Glow wire test according to CEI 695-2-1: 650°C

Impact strength IK01

Identification

Range essensya