



WE300



Double switch for shutters Essensya Pure

Technical properties

Architecture

Number of poles	1 P
Type of control unit	double rocker

Controls and indicators

Number of buttons	2
Venetian blind switch type	2-pole switch

Main electrical features

Nominal voltage	250 V
-----------------	-------

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	37 mm
Height of installed product	75 mm
Width of installed product	75 mm

Capacity

Number of module locations	0
----------------------------	---

Materials

Surface appearance	glossy
Type of surface treatment	untreated

Installation, mounting

Fixing type	With screws
-------------	-------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Identification

Composition	Mechanism with upper casing
-------------	-----------------------------