



WE310



Electronic thermostat Essensya Pure

Technical properties

Architecture

Fixing mode Clipped

Functions

With cooling function Yes

Dimensions

Internal depth 50 mm

Measurement

Temperature measurement range 5 / 40 °C

Capacity

Number of modules for WA 2

Power supply

Supply voltage 230 V AC

Materials

Colour white

Settings

Comfort temperature setpoint 5 / 30 °C

Equipment

Type of probe sensor with resistor

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range essensya