



WE310T



## Electronic thermostat Essensya Titane

### Technical properties

#### Architecture

Fixing mode Clipped

#### Functions

With cooling function Yes

#### Dimensions

Internal depth 50 mm

#### Measurement

Temperature measurement range 5 / 40 °C

#### Capacity

Number of modules for WA 2

#### Settings

Comfort temperature setpoint 5 / 30 °C

#### Equipment

Type of probe sensor with resistor

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range essensya