



WE314

Essensya Thermostat pilot wire

Technical properties

Configuration

Static differential	0,5°C
---------------------	-------

Main electrical features

Rated operational voltage Ue	230 / 250 V
Adjustable nominal current	8 A
Frequency	50 Hz

Electric current

Rated current	8 A
---------------	-----

Dimensions

Internal depth	51.5 mm
Height of installed product	70 mm
Width of installed product	70 mm
Dimensions of installed product	51.5

Capacity

Number of modules for WA	2
--------------------------	---

Power supply

Supply voltage	230 V
----------------	-------

Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white

Installation, mounting

Maximum Mounting Height	1.5 m
Mounting type	flush-mounted

Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm ²
Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of connection	with screw

Settings

Comfort temperature setpoint	5 / 30 °C
------------------------------	-----------

Equipment

With fall in temperature	1
On/Off switch	Yes
Electronic control	1
Type of thermostat	thermostat
Switch or lamp for fall in temperature of night	0
Type of probe	temperature sensor

Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	essensya
-------	----------