



WE314

Essensya Thermostat pilot wire

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Rated operational voltage Ue	230 / 250 V
Adjustable nominal current	8 A
Frequency	50 Hz

Electric current

Rated current	8 A
---------------	-----

Dimensions

Internal depth	51.5 mm
Height of installed product	70 mm
Width of installed product	70 mm
Dimensions of installed product	51.5

Capacity

Number of modules for WA	2
--------------------------	---

Power supply

Supply voltage	230 V
----------------	-------

Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white

Installation, mounting

Maximum Mounting Height	1.5 m
-------------------------	-------

Settings

Comfort temperature setpoint	5 / 30 °C
------------------------------	-----------

Equipment

With fall in temperature	1
On/Off switch	Yes
Electronic control	1
Switch or lamp for fall in temperature of night	0
Type of probe	temperature sensor

Safety

IK protection code against mechanical impacts

07

Protection index IP

IP20

Use conditions

Operating temperature

-10...35 °C

Storage/transport temperature

-10...50 °C

Identification

Range

essensya