



WE401

## 1G Plate Essensya Pure

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Dimensions

Internal depth	0 mm
Height of installed product	80 mm
Width of installed product	80 mm
Width	80 mm

#### Capacity

Number of sockets	1
Number of gang in horizontal	1
Number of modules (horizontal)	2
Number of modules (vertical)	2

#### Materials

Free area for finishing name	pure
Colour	white
Material	polycarbonate
Type of surface treatment	untreated
Transparent	No

#### Installation, mounting

Mounting way	vertical and horizontal
--------------	-------------------------

#### Equipment

With mounting frame or grid	No
With transparent product label holder	No

#### Safety

Protection index IP	IP20
---------------------	------

#### Identification

Range	essensya
-------	----------