



WE404

## 4G Plate Essensya entraxe 71mm Pure

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Dimensions

Internal depth	0 mm
Height of installed product	80 mm
Width of installed product	80 mm

#### Capacity

Number of sockets	4
Number of gang in horizontal	4
Number of modules (horizontal)	8
Number of modules (vertical)	8

#### Materials

Free area for finishing name	pure
Colour	white
Material	polycarbonate
Surface appearance	glossy
Type of surface treatment	untreated
Transparent	No

#### Installation, mounting

Fixing type	clik - connection
Mounting way	vertical and horizontal

#### Equipment

With mounting frame or grid	No
With transparent product label holder	No

#### Safety

IK protection code against mechanical impacts	IK05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Identification

Range	essensya
-------	----------