



WNA001

cubyko 2-way switch composable grey IP55

Technical properties

Architecture

Type of order	Switch
Type of control unit	single rocker
Fixing mode	Clipped

Configuration

Switch mode	2 way
-------------	-------

Controls and indicators

Indicator lamp	no
Push-buttons	No

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Material	polypropylène
----------	---------------

Installation, mounting

Mounting type	flush mounted / surface mounted
---------------	---------------------------------

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	2 way
Type of connection	Quickconnect

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Standards

Approvals

EN 60669-1

Safety

IK protection code against mechanical impacts

07

REACH conform

Yes

RoHS conform

Yes

Halogen free

Yes

Impact strength

IK07

Use conditions

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

Identification

Range

cubyko

Composition

Mechanism with upper casing

Pictograms

Symbole WA

INSTALLATEUR.JPG