



WNA001

cubyko 2-way switch composable grey IP55

Technical properties

Architecture

| | |
|----------------------|---------------|
| Type of control unit | single rocker |
| Fixing mode | Clipped |

Controls and indicators

| | |
|----------------|----|
| Indicator lamp | no |
| Push-buttons | No |

Main electrical features

| | |
|-----------|----------|
| Frequency | 50/60 Hz |
|-----------|----------|

Electric current

| | |
|---------------|-------|
| Rated current | 10 AX |
|---------------|-------|

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 40 mm |
| Height of installed product | 75 mm |
| Width of installed product | 75 mm |

Capacity

| | |
|--------------------------|---|
| Number of modules for WA | 2 |
|--------------------------|---|

Materials

| | |
|------------|----------------------|
| RAL colour | RAL 7011 - Iron grey |
| Material | polypropylène |
| Material | Mixed materials |

Connection

| | |
|--------------------|--------------|
| Type of connection | Quickconnect |
|--------------------|--------------|

Equipment

| | |
|----------------|--|
| Lighting | without lighting (cannot be illuminated) |
| Heating switch | No |

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | 07 |
| Protection index IP | IP55 |
| Impact strength | IK07 |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -15...30 °C |
|-----------------------|-------------|

Storage/transport temperature

-50...50 °C

Identification

Range

cubyko

Composition

Mechanism with upper casing

Pictograms

Symbole WA

INSTALLATEUR.JPG