



WNA002

cubyko 2-way switch illuminated composable grey IP55

Technical properties

Architecture

Type of control unit	single rocker
Fixing mode	Clipped

Controls and indicators

Indicator lamp	yes
Push-buttons	No

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

RAL colour	RAL 7011 - Iron grey
Material	polypropylène
Material	Mixed materials

Connection

Type of connection	Quickconnect
--------------------	--------------

Equipment

Lighting	for illumination
Heating switch	No

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP55
Impact strength	IK07

Use conditions

Operating temperature	-15...30 °C
-----------------------	-------------

Storage/transport temperature

-50...50 °C

Identification

Range

cubyko

Composition

Mechanism with upper casing

Pictograms

Symbole WA

INSTALLATEUR.JPG