



WNA002B

## Cubyko LT 2-way switch illuminated composable white IP55

### Technical properties

#### Architecture

Fixing mode Clipped

#### Controls and indicators

Indicator lamp yes

#### Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

#### Electric current

Rated current 10 AX

#### Dimensions

Depth of installed product 40 mm

Height of installed product 75 mm

Width of installed product 75 mm

#### Capacity

Number of modules for WA 2

#### Materials

RAL colour RAL 9010 - Pure white

Material polypropylène

#### Installation, mounting

Mounting type flush-mounted

#### Connection

Connection cross-sect. rigid cable mini 2x1 mm<sup>2</sup> - maxi 2x2,5 mm<sup>2</sup>

Type of connection quick connect

#### Equipment

Heating switch No

#### Standards

Approvals EN 60669-1

#### Safety

IK protection code against mechanical impacts 07

REACH conform Yes

RoHS conform	Yes
Halogen free	No
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
<b>Identification</b>	
Range	cubyko
Composition	Mechanism with upper casing