



WNA002B

Cubyko LT 2-way switch illuminated composable white IP55

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Nominal voltage	250 V
-----------------	-------

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	40 mm
----------------------------	-------

Height of installed product	75 mm
-----------------------------	-------

Width of installed product	75 mm
----------------------------	-------

Capacity

Number of modules for WA	2
--------------------------	---

Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	polypropylène
----------	---------------

Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
------------------------------------	---

Type of connection	quick connect
--------------------	---------------

Equipment

Heating switch	No
----------------	----

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	07
---	----

REACH conform	Yes
---------------	-----

RoHS conform	Yes
Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Identification	
Range	cubyko
Composition	Mechanism with upper casing