



WNA002B

**cubyko 2W SW illuminated compos. white**

**Technical properties**

**Architecture**

Type of control unit	single rocker
Fixing mode	Clipped

**Controls and indicators**

Indicator lamp	yes
Push-buttons	No

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 AX
---------------	-------

**Dimensions**

Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

RAL colour	RAL 9010 - Pure white
Material	Mixed materials

**Connection**

Type of connection	Quickconnect
--------------------	--------------

**Equipment**

Lighting	for illumination
Heating switch	No

**Safety**

IK protection code against mechanical impacts	07
Protection index IP	IP55
Impact strength	IK07

**Use conditions**

Operating temperature	-15...30 °C
-----------------------	-------------

