



WNA003

**cubyko 2-way with control light composable grey IP55**

**Technical properties**

**Architecture**

Type of control unit	single rocker
Number of keys	2
Fixing mode	Clipped

**Controls and indicators**

Indicator lamp	yes
Push-buttons	No

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 AX
---------------	-------

**Dimensions**

Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

RAL colour	RAL 7011 - Iron grey
Material	Mixed materials

**Connection**

Type of connection	Quickconnect
--------------------	--------------

**Equipment**

Lighting	for illumination
Heating switch	No

**Safety**

IK protection code against mechanical impacts	07
Protection index IP	IP55
REACH conform	Yes
RoHS conform	Yes

Halogen free	No
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
<b>Pictograms</b>	
Symbole WA	INSTALLATEUR.JPG