



WNA003

**cubyko 2-way with control light composable grey IP55**

**Technical properties**

**Architecture**

Type of order	Switch
Type of control unit	single rocker
Number of keys	2
Fixing mode	Clipped

**Configuration**

Switch mode	2 way, with loop terminal
-------------	---------------------------

**Controls and indicators**

Indicator lamp	yes
Push-buttons	No

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 AX
---------------	-------

**Dimensions**

Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

Material	polypropylène
----------	---------------

**Installation, mounting**

Mounting type	flush mounted / surface mounted
---------------	---------------------------------

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Connection type	quick connect
Type of contacts	2 way
Type of connection	Quickconnect

**Equipment**

Lighting	for illumination
Heating switch	No
<b>Standards</b>	
Approvals	EN 60669-1
<b>Safety</b>	
IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
<b>Identification</b>	
Range	cubyko
Composition	Mechanism with upper casing
<b>Pictograms</b>	
Symbole WA	INSTALLATEUR.JPG