



WNA003B

Cubyko LT 2-way switch with control light composable white IP55

Technical properties

Architecture

Number of keys	2
Fixing mode	Clipped

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

RAL colour	RAL 9010 - Pure white
Material	polypropylène

Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of connection	quick connect

Equipment

Heating switch	No
----------------	----

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	07
---	----

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Range	cubyko
Composition	Mechanism with upper casing