



WNA003B

**Cubyko LT 2-way switch with control light composable white IP55**

**Technical properties**

**Architecture**

Number of keys	2
Fixing mode	Clipped

**Controls and indicators**

Indicator lamp	yes
----------------	-----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 AX
---------------	-------

**Dimensions**

Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

RAL colour	RAL 9010 - Pure white
Material	polypropylène

**Installation, mounting**

Mounting type	flush-mounted
---------------	---------------

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of connection	quick connect

**Equipment**

Heating switch	No
----------------	----

**Standards**

Approvals	EN 60669-1
-----------	------------

**Safety**

IK protection code against mechanical impacts	07
---	----

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

---

**Use conditions**

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

---

**Identification**

Range	cubyko
Composition	Mechanism with upper casing