



WNA003B

Cubyko LT 2-way switch with control light composable white IP55

Technical properties

Architecture

Fixing mode Clipped

Controls and indicators

Indicator lamp yes

Main electrical features

Frequency 50/60 Hz

Electric current

Rated current 10 AX

Dimensions

Depth of installed product 40 mm

Height of installed product 75 mm

Width of installed product 75 mm

Capacity

Number of modules for WA 2

Materials

RAL colour RAL 9010 - Pure white

Material polypropylène

Equipment

Heating switch No

Safety

IK protection code against mechanical impacts 07

Protection index IP IP20

Impact strength IK07

Use conditions

Operating temperature -15...30 °C

Storage/transport temperature -50...50 °C

Identification

Range cubyko

Composition Mechanism with upper casing