



WNA006

cubyko 2W SW +label holder compos. grey

Technical properties

Architecture

Type of order	Switch
Type of control unit	Push button
Fixing mode	Clipped

Configuration

Switch mode	2 way
-------------	-------

Controls and indicators

Indicator lamp	yes
Push-buttons	No

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	compos. grey
RAL colour	RAL 7011 - Iron grey
Material	polypropylène
Material	Mixed materials
Type of surface treatment	mat varnish

Installation, mounting

Mounting type	flush mounted / surface mounted
---------------	---------------------------------

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	2 way
Type of connection	Quickconnect

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP55
Impact strength	IK07

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Range	cubyko
Composition	Mechanism with upper casing
