



WNA006B

**cubyko 2W SW +label holder compos. white**

**Technical properties**

**Architecture**

Type of order	Switch
Type of control unit	single rocker
Fixing mode	Clipped

**Configuration**

Switch mode	2 way
-------------	-------

**Controls and indicators**

Indicator lamp	yes
Push-buttons	No

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 AX
---------------	-------

**Dimensions**

Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

RAL colour	RAL 9010 - Pure white
Material	polypropylène

**Installation, mounting**

Mounting type	flush mounted / surface mounted
---------------	---------------------------------

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of contacts	2 way
Type of connection	Quickconnect

**Equipment**

Lighting	without lighting (cannot be illuminated)
----------	--

Heating switch

No

---

**Standards**

Approvals

EN 60669-1

---

**Safety**

IK protection code against mechanical impacts

07

Impact strength

IK07

---

**Use conditions**

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

---

**Identification**

Range

cubyko

Composition

Mechanism with upper casing