



WNA008

**Cubyko LT 2-pole marked 0/1 composable grey IP55**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Controls and indicators**

Indicator lamp no

**Main electrical features**

Nominal voltage 250 V

Frequency 50/60 Hz

**Electric current**

Rated current 10 AX

**Dimensions**

Depth of installed product 40 mm

Height of installed product 75 mm

Width of installed product 75 mm

**Capacity**

Number of modules for WA 2

**Materials**

Material polypropylène

**Installation, mounting**

Mounting type flush-mounted

**Connection**

Connection cross-sect. rigid cable mini 2x1 mm<sup>2</sup> - maxi 2x2,5 mm<sup>2</sup>

Type of connection quick connect

**Equipment**

Heating switch No

**Standards**

Approvals EN 60669-1

**Safety**

IK protection code against mechanical impacts 07

REACH conform Yes

RoHS conform Yes

|                               |                             |
|-------------------------------|-----------------------------|
| Halogen free                  | Yes                         |
| Impact strength               | IK07                        |
| <b>Use conditions</b>         |                             |
| Operating temperature         | -15...30 °C                 |
| Storage/transport temperature | -50...50 °C                 |
| <b>Identification</b>         |                             |
| Range                         | cubyko                      |
| Composition                   | Mechanism with upper casing |
| <b>Pictograms</b>             |                             |
| Symbole WA                    | INSTALLATEUR.JPG            |