



WNA008B



Cubyko LT 2-pole marked 0/1 composable white IP55

Technical properties

Architecture

Fixing mode Clipped

Controls and indicators

Indicator lamp no

Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

Electric current

Rated current 10 AX

Dimensions

Depth of installed product 40 mm

Height of installed product 75 mm

Width of installed product 75 mm

Capacity

Number of modules for WA 2

Materials

RAL colour RAL 9010 - Pure white

Material polypropylène

Installation, mounting

Mounting type flush-mounted

Connection

Connection cross-sect. rigid cable mini 2x1 mm² - maxi 2x2,5 mm²

Type of connection quick connect

Equipment

Heating switch No

Standards

Approvals EN 60669-1

Safety

IK protection code against mechanical impacts 07

REACH conform Yes

RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07
Use conditions	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Identification	
Range	cubyko
Composition	Mechanism with upper casing