



WNA008B



**Cubyko LT 2-pole marked 0/1 composable white IP55**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Controls and indicators**

Indicator lamp	no
----------------	----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 AX
---------------	-------

**Dimensions**

Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

RAL colour	RAL 9010 - Pure white
------------	-----------------------

**Installation, mounting**

Mounting type	flush-mounted
---------------	---------------

**Connection**

Type of connection	quick connect
--------------------	---------------

**Equipment**

Heating switch	No
----------------	----

**Safety**

IK protection code against mechanical impacts	07
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

**Use conditions**

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C