



WNA010

Cubyko LT intermediate switch composable grey IP55

Technical properties

Architecture

Number of keys	1
Fixing mode	Clipped

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

Materials

RAL colour	RAL 7011 - Iron grey
------------	----------------------

Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Connection

Type of connection	quick connect
--------------------	---------------

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C