



WNA010

## Cubyko LT intermediate switch composable grey IP55

### Technical properties

#### Architecture

|                |         |
|----------------|---------|
| Number of keys | 1       |
| Fixing mode    | Clipped |

#### Controls and indicators

|                |    |
|----------------|----|
| Indicator lamp | no |
|----------------|----|

#### Main electrical features

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Frequency       | 50/60 Hz |

#### Electric current

|               |       |
|---------------|-------|
| Rated current | 10 AX |
|---------------|-------|

#### Dimensions

|                                         |       |
|-----------------------------------------|-------|
| Installation depth, flush-mounted boxes | 40 mm |
| Depth of installed product              | 40 mm |
| Height of installed product             | 75 mm |
| Width of installed product              | 75 mm |

#### Materials

|          |               |
|----------|---------------|
| Material | polypropylène |
|----------|---------------|

#### Installation, mounting

|               |                 |
|---------------|-----------------|
| Fixing type   | turn screw lock |
| Mounting type | flush-mounted   |

#### Connection

|                                    |                                                       |
|------------------------------------|-------------------------------------------------------|
| Connection cross-sect. rigid cable | mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup> |
| Type of connection                 | quick connect                                         |

#### Standards

|           |            |
|-----------|------------|
| Approvals | EN 60669-1 |
|-----------|------------|

#### Safety

|                                               |      |
|-----------------------------------------------|------|
| IK protection code against mechanical impacts | 07   |
| REACH conform                                 | Yes  |
| RoHS conform                                  | Yes  |
| Halogen free                                  | Yes  |
| Impact strength                               | IK07 |

**Use conditions**

---

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -15...30 °C |
| Storage/transport temperature | -50...50 °C |

---

**Identification**

---

|             |                             |
|-------------|-----------------------------|
| Range       | cubyko                      |
| Composition | Mechanism with upper casing |

---