



WNA020B

Cubyko LT push-button 1F composable white IP55

Technical properties

Architecture

Number of keys	1
Fixing mode	Clipped

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

Materials

RAL colour	RAL 9010 - Pure white
Material	polypropylène

Installation, mounting

Fixing type	turn screw lock
Mounting type	flush-mounted

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of connection	quick connect

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

Identification

Range

cubyko

Composition

Mechanism with upper casing