



WNA020B

**cubyko PB 1F compos. white**

**Technical properties**

**Architecture**

Number of keys	1
Fixing mode	Clipped

**Controls and indicators**

Indicator lamp	no
----------------	----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 A
---------------	------

**Dimensions**

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

**Materials**

RAL colour	RAL 9010 - Pure white
Material	polypropylène

**Connection**

Type of contacts	1NO
Type of connection	Quickconnect

**Safety**

IK protection code against mechanical impacts	07
Protection index IP	IP55
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

**Use conditions**

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

