



WNA021

cubyko Push-button 10/1F illuminated composable grey IP55

Technical properties

Architecture

Type of control unit	Push button
Number of keys	1
Fixing mode	Clipped

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

Materials

Material	polypropylène
----------	---------------

Installation, mounting

Fixing type	turn screw lock
Mounting type	flush mounted / surface mounted

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	1NC+1NO
Type of connection	Quickconnect

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes

Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Identification	
Range	cubyko
Composition	Mechanism with upper casing