



WNA021

cubyko Push-button 10/1F illuminated composable grey IP55

Technical properties

Architecture

| | |
|----------------|---------|
| Number of keys | 1 |
| Fixing mode | Clipped |

Controls and indicators

| | |
|----------------|-----|
| Indicator lamp | yes |
|----------------|-----|

Main electrical features

| | |
|-----------|----------|
| Frequency | 50/60 Hz |
|-----------|----------|

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Dimensions

| | |
|---|-------|
| Installation depth, flush-mounted boxes | 40 mm |
| Depth of installed product | 40 mm |
| Height of installed product | 75 mm |
| Width of installed product | 75 mm |

Materials

| | |
|------------|----------------------|
| RAL colour | RAL 7011 - Iron grey |
| Material | polypropylène |

Connection

| | |
|--------------------|--------------|
| Type of connection | Quickconnect |
|--------------------|--------------|

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | 07 |
| Protection index IP | IP55 |
| Impact strength | IK07 |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -15...30 °C |
| Storage/transport temperature | -50...50 °C |

Identification

| | |
|-------------|-----------------------------|
| Range | cubyko |
| Composition | Mechanism with upper casing |