



WNA021B

Cubyko LT push-button 10/1F illuminated composable white IP55

Technical properties

Architecture

Number of keys	1
Fixing mode	Clipped

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	10 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

Materials

RAL colour	RAL 9010 - Pure white
Material	polypropylène

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP20
Impact strength	IK07

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Range	cubyko
Composition	Mechanism with upper casing