



WNA021B

## Cubyko LT push-button 10/1F illuminated composable white IP55

### Technical properties

#### Architecture

Number of keys	1
Fixing mode	Clipped

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

#### Electric current

Rated current	10 A
---------------	------

#### Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

#### Materials

RAL colour	RAL 9010 - Pure white
Material	polypropylène

#### Installation, mounting

Fixing type	turn screw lock
Mounting type	flush-mounted

#### Connection

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of connection	quick connect

#### Standards

Approvals	EN 60669-1
-----------	------------

#### Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

**Identification**

Range

cubyko

Composition

Mechanism with upper casing