



WNA023B

## Cubyko LT push-button 1F with control light composable white IP55

### Technical properties

#### Architecture

Number of keys	1
Fixing mode	Clipped

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Electric current

Rated current	10 A
---------------	------

#### Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

#### Capacity

Number of modules for WA	2
--------------------------	---

#### Materials

RAL colour	RAL 9010 - Pure white
Material	polypropylène

#### Safety

IK protection code against mechanical impacts	07
Protection index IP	IP20
Impact strength	IK07

#### Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

#### Identification

Range	cubyko
Composition	Mechanism with upper casing