



WNA025

cubyko PB 1F w. FPL compos. grey

Technical properties

Architecture

Type of order	Push button
Type of control unit	Push button
Number of keys	1
Fixing mode	Clipped

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Nominal voltage	24V
Frequency	50/60 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	compos. grey
RAL colour	RAL 7011 - Iron grey
Material	polypropylène
Material	Polypropylen
Type of surface treatment	mat

Installation, mounting

Fixing type	turn screw lock
Mounting type	flush mounted / surface mounted

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	1NC+1NO
Type of connection	Quickconnect

Standards

Approvals

EN 60669-1

Safety

IK protection code against mechanical impacts

07

Protection index IP

IP55

Impact strength

IK07

Use conditions

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

Identification

Range

cubyko

Composition

Mechanism with upper casing

Pictograms

Symbole WA

INSTALLATEUR.JPG