



WNA025B

**Cubyko LT push-button 1F with label holder composable white IP55**

**Technical properties**

**Architecture**

Number of keys	1
Fixing mode	Clipped

**Controls and indicators**

Indicator lamp	yes
----------------	-----

**Main electrical features**

Frequency	50/60 Hz
-----------	----------

**Electric current**

Rated current	10 A
---------------	------

**Dimensions**

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

RAL colour	RAL 9010 - Pure white
Material	polypropylène

**Safety**

IK protection code against mechanical impacts	07
Protection index IP	IP20
Impact strength	IK07

**Use conditions**

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

**Identification**

Range	cubyko
Composition	Mechanism with upper casing