



WNA032

cubyko Emergency switch key version grey IP55

Technical properties

Architecture

Type of order	Push button
Type of control unit	Key
Number of keys	1
Fixing mode	Clipped

Controls and indicators

Indicator lamp	no
Push-buttons	No

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	85 mm
Height of installed product	75 mm
Width of installed product	75 mm

Materials

Material	polypropylène
----------	---------------

Installation, mounting

Mounting type	flush mounted / surface mounted
---------------	---------------------------------

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of connection	quick connect

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	07
---	----

REACH conform	Yes
RoHS conform	Yes
Impact strength	IK07

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Range	cubyko
Composition	Mechanism with upper casing