



WNA032

cubyko Emergency switch key version grey IP55

Technical properties

Architecture

Type of order	Push button
Type of control unit	Key
Number of keys	1
Fixing mode	Clipped

Controls and indicators

Indicator lamp	no
Push-buttons	No

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	85 mm
Height of installed product	75 mm
Width of installed product	75 mm

Materials

Colour	composable grey
RAL colour	RAL 7011 - Iron grey
Material	polypropylène
Material	Polypropylen
Type of surface treatment	mat varnish

Installation, mounting

Mounting type	flush mounted / surface mounted
---------------	---------------------------------

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of connection	quick connect

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Standards

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP55
Impact strength	IK07

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Range	cubyko
Composition	Mechanism with upper casing
