



WNA033

**cubyko Emergency switch grey IP55**

**Technical properties**

**Architecture**

Type of order	Push button
Type of control unit	Push & rotative
Number of keys	1
Fixing mode	Clipped

**Controls and indicators**

Indicator lamp	no
Push-buttons	No

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 AX
---------------	-------

**Dimensions**

Depth of installed product	85 mm
Height of installed product	75 mm
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

Colour	composable grey
RAL colour	RAL 7011 - Iron grey
Material	polypropylène
Material	Polypropylen
Type of surface treatment	mat varnish

**Installation, mounting**

Mounting type	flush mounted / surface mounted
---------------	---------------------------------

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of contacts	1NC+1NO
Type of connection	quick connect

**Equipment**

Lighting	without lighting (cannot be illuminated)
Heating switch	No
<b>Standards</b>	
Approvals	EN 60669-1
<b>Safety</b>	
IK protection code against mechanical impacts	07
Protection index IP	IP55
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
<b>Identification</b>	
Range	cubyko
Composition	Mechanism with upper casing