



WNA033

cubyko Emergency switch grey IP55

Technical properties

Architecture

Type of order	Push button
Type of control unit	Push & rotative
Number of keys	1
Fixing mode	Clipped

Controls and indicators

Indicator lamp	no
Push-buttons	No

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	85 mm
Height of installed product	75 mm
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Material	polypropylène
----------	---------------

Installation, mounting

Mounting type	flush mounted / surface mounted
---------------	---------------------------------

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	1NC+1NO
Type of connection	quick connect

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Standards

Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Impact strength	IK07

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Range	cubyko
Composition	Mechanism with upper casing