



WNA040B

Cubyko LT 2-gang 2-way switch composable white IP55

Technical properties

Architecture

| | |
|----------------|---------|
| Number of keys | 2 |
| Fixing mode | Clipped |

Controls and indicators

| | |
|----------------|-----------------|
| Indicator lamp | as an accessory |
|----------------|-----------------|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Frequency | 50/60 Hz |

Electric current

| | |
|---------------|-------|
| Rated current | 10 AX |
|---------------|-------|

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 40 mm |
| Height of installed product | 75 mm |
| Width of installed product | 75 mm |

Capacity

| | |
|--------------------------|---|
| Number of modules for WA | 2 |
|--------------------------|---|

Materials

| | |
|------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
| Material | polypropylène |

Installation, mounting

| | |
|---------------|---------------|
| Mounting type | flush-mounted |
|---------------|---------------|

Connection

| | |
|------------------------------------|---|
| Connection cross-sect. rigid cable | mini 2x1 mm ² - maxi 2x2,5 mm ² |
| Type of connection | quick connect |

Equipment

| | |
|----------------|----|
| Heating switch | No |
|----------------|----|

Standards

| | |
|-----------|------------|
| Approvals | EN 60669-1 |
|-----------|------------|

Safety

| | |
|---|----|
| IK protection code against mechanical impacts | 07 |
|---|----|

| | |
|-----------------|------|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |
| Impact strength | IK07 |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -15...30 °C |
| Storage/transport temperature | -50...50 °C |

Identification

| | |
|-------------|-----------------------------|
| Range | cubyko |
| Composition | Mechanism with upper casing |