



WNA044

**Cubyko LT 2-gang 2-way push-button 10/1F composable grey IP55**

**Technical properties**

**Architecture**

Number of keys	2
Fixing mode	Clipped

**Controls and indicators**

Indicator lamp	as an accessory
----------------	-----------------

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	10 A
---------------	------

**Dimensions**

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

Material	polypropylène
----------	---------------

**Installation, mounting**

Fixing type	turn screw lock
Mounting type	flush-mounted

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of connection	quick connect

**Standards**

Approvals	EN 60669-1
-----------	------------

**Safety**

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes

Halogen free	Yes
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
<b>Identification</b>	
Range	cubyko
Composition	Mechanism with upper casing