



WNA044

cubyko 2-gang 2W PB 10/1F compos. grey

Technical properties

Architecture

Type of control unit	double push button
Number of keys	2
Fixing mode	Clipped

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	40 mm
Height of installed product	75 mm
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

RAL colour	RAL 7011 - Iron grey
------------	----------------------

Connection

Type of connection	Quickconnect
--------------------	--------------

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP55
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C