



WNA044B

Cubyko LT 2-gang 2-way push-button 10/1F composable white IP55

Technical properties

Architecture

Fixing mode Clipped

Main electrical features

Frequency 50/60 Hz

Electric current

Rated current 10 A

Dimensions

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 40 mm

Height of installed product 75 mm

Width of installed product 75 mm

Capacity

Number of modules for WA 2

Materials

RAL colour RAL 9010 - Pure white

Material polypropylène

Safety

IK protection code against mechanical impacts 07

Protection index IP IP20

Impact strength IK07

Use conditions

Operating temperature -15...30 °C

Storage/transport temperature -50...50 °C

Identification

Range cubyko

Composition Mechanism with upper casing