



WNA100B

**cubyko Socket 2P+E composable white IP55**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Functions**

Centralized terminal connections	No
With orientation lighting	No
Overvoltage protection	No

**Compatibility**

IFTTT support available	No
-------------------------	----

**Controls and indicators**

Indicator lamp	no
With or without indicator	without

**Connectivity**

With USB charging socket	No
--------------------------	----

**Main electrical features**

Frequency	50/60 Hz
-----------	----------

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	22.8 mm
Height of installed product	75 mm
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
Number of module locations	2

**Cover, door**

Interlockable	No
---------------	----

**Power supply**

Special power supply	No special power supply
----------------------	-------------------------

**Materials**

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Transparent	No
Metallic colour	No
<b>Connection</b>	
Type of connection	Quickconnect
<b>Accessories included</b>	
With miniature fuse	No
<b>Equipment</b>	
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No
<b>Safety</b>	
IK protection code against mechanical impacts	07
Protection index IP	IP55
<b>Use conditions</b>	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes
<b>Identification</b>	
Range	cubyko