



WNA104

**cubyko Socket 2P+E with label holder composable grey IP55**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Functions**

Centralized terminal connections No

With orientation lighting No

Overvoltage protection No

**Compatibility**

IFTTT support available No

**Controls and indicators**

Indicator lamp no

With or without indicator without

**Connectivity**

With USB charging socket No

**Main electrical features**

Frequency 50/60 Hz

**Electric current**

Rated current 16 A

**Dimensions**

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 22.8 mm

Height of installed product 75 mm

Width of installed product 75 mm

**Capacity**

Number of modules for WA 2

Number of module locations 2

**Cover, door**

Interlockable No

**Power supply**

Special power supply No special power supply

**Materials**

RAL colour RAL 7011 - Iron grey

Transparent	No
Metallic colour	No
<b>Connection</b>	
Type of connection	Quickconnect
<b>Accessories included</b>	
With miniature fuse	No
<b>Equipment</b>	
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	Yes
<b>Safety</b>	
IK protection code against mechanical impacts	07
Protection index IP	IP55
<b>Use conditions</b>	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes
<b>Identification</b>	
Range	cubyko