



WNA104

**cubyko Socket 2P+E with label holder composable grey IP55**

**Technical properties**

**Architecture**

Type of pole	2P+T
Fixing mode	Clipped

**Functions**

Centralized terminal connections	No
With orientation lighting	No
Overvoltage protection	No

**Compatibility**

IFTTT support available	No
-------------------------	----

**Controls and indicators**

Indicator lamp	no
With or without indicator	without

**Connectivity**

With USB charging socket	No
--------------------------	----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	22.8 mm
Height of installed product	75 mm
Width of installed product	75 mm

**Capacity**

Number of modules for WA	2
Number of module locations	2

**Cover, door**

Interlockable	No
---------------	----

**Power supply**

Special power supply	No special power supply
----------------------	-------------------------

**Materials**

Material quality	Material mix
Surface appearance	satin finish
Transparent	No
Metallic colour	No

**Installation, mounting**

Fixing type	turn screw lock
Mounting type	flush mounted / surface mounted

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Phase pickup	L1
Type of connection	Quickconnect

**Accessories included**

With miniature fuse	No
---------------------	----

**Equipment**

Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	Yes

**Standards**

Approvals	NFC 61314
-----------	-----------

**Safety**

IK protection code against mechanical impacts	07
Protection	without protective screen

**Use conditions**

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes

**Identification**

Range	cubyko
-------	--------