



WNA105

**cubyko Socket 2P+E detrompage composable grey IP55**

**Technical properties**

**Architecture**

|              |         |
|--------------|---------|
| Type of pole | 2P+T    |
| Fixing mode  | Clipped |

**Functions**

|                                  |    |
|----------------------------------|----|
| Centralized terminal connections | No |
| With orientation lighting        | No |
| Overvoltage protection           | No |

**Compatibility**

|                         |    |
|-------------------------|----|
| IFTTT support available | No |
|-------------------------|----|

**Controls and indicators**

|                           |         |
|---------------------------|---------|
| Indicator lamp            | no      |
| With or without indicator | without |

**Connectivity**

|                          |    |
|--------------------------|----|
| With USB charging socket | No |
|--------------------------|----|

**Main electrical features**

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Frequency       | 50/60 Hz |

**Electric current**

|                           |      |
|---------------------------|------|
| Measurement error current | 0 mA |
| Rated current             | 16 A |

**Dimensions**

|   |         |
|---|---------|
| Installation depth, flush-mounted boxes | 35 mm   |
| Depth of installed product              | 22.8 mm |
| Height of installed product             | 75 mm   |
| Width of installed product              | 75 mm   |

**Capacity**

|                            |   |
|----------------------------|---|
| Number of modules for WA   | 2 |
| Number of module locations | 2 |

**Cover, door**

|               |    |
|---------------|----|
| Interlockable | No |
|---------------|----|

**Power supply**

**Materials**

|                           |              |
|---------------------------|--------------|
| Material quality          | Material mix |
| Surface appearance        | satin finish |
| Type of surface treatment | untreated    |
| Transparent               | No           |
| Metallic colour           | No           |

**Installation, mounting**

|               |                                 |
|---------------|---------------------------------|
| Fixing type   | turn screw lock                 |
| Mounting type | flush mounted / surface mounted |

**Connection**

|                                    |   |
|------------------------------------|---|
| Connection cross-sect. rigid cable | mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup> |
| Phase pickup                       | L1  |
| Type of connection                 | Quickconnect  |

**Accessories included**

|                     |    |
|---------------------|----|
| With miniature fuse | No |
|---------------------|----|

**Equipment**

|                                       |    |
|---------------------------------------|----|
| Number of units                       | 1  |
| Number of socket outlets switchable   | 0  |
| On/Off switch                         | No |
| With transparent product label holder | No |

**Standards**

|           |           |
|-----------|-----------|
| Approvals | NFC 61314 |
|-----------|-----------|

**Safety**

|   |                           |
|---|---------------------------|
| IK protection code against mechanical impacts | 07                        |
| Protection                                    | without protective screen |

**Use conditions**

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -15...30 °C |
| Storage/transport temperature | -50...50 °C |
| Insulated                     | Yes         |

**Identification**

|       |        |
|-------|--------|
| Range | cubyko |
|-------|--------|