



WNA105

cubyko Socket 2P+E detrompage composable grey IP55

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Functions

Centralized terminal connections	No
With orientation lighting	No
Overvoltage protection	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Indicator lamp	no
With or without indicator	without

Connectivity

With USB charging socket	No
--------------------------	----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Measurement error current	0 mA
Rated current	16 A

Dimensions

Installation depth, flush-mounted boxes	35 mm
Depth of installed product	22.8 mm
Height of installed product	75 mm
Width of installed product	75 mm

Capacity

Number of modules for WA	2
Number of module locations	2

Cover, door

Interlockable	No
---------------	----

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

RAL colour	RAL 7011 - Iron grey
Type of surface treatment	untreated
Transparent	No
Metallic colour	No
Connection	
Type of connection	Quickconnect
Accessories included	
With miniature fuse	No
Equipment	
Number of units	1
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No
Safety	
IK protection code against mechanical impacts	07
Protection index IP	IP55
Use conditions	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes
Identification	
Range	cubyko