



WNA105B

## cubyko Socket 2P+E detrompage composable white IP55

### Technical properties

#### Architecture

Type of pole	2P+T
Fixing mode	Clipped

#### Functions

Centralized terminal connections	No
With orientation lighting	No
Overvoltage protection	No

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Controls and indicators

Indicator lamp	no
With or without indicator	without

#### Connectivity

With USB charging socket	No
--------------------------	----

#### Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

#### Electric current

Measurement error current	0 mA
Rated current	16 A

#### Dimensions

Installation depth, flush-mounted boxes	35 mm
Depth of installed product	22.8 mm
Height of installed product	75 mm
Width of installed product	75 mm

#### Capacity

Number of modules for WA	2
Number of module locations	2

#### Cover, door

Interlockable	No
---------------	----

#### Power supply

Special power supply

No special power supply

### Materials

RAL colour	RAL 9010 - Pure white
Material quality	Material mix
Surface appearance	satin finish
Type of surface treatment	untreated
Transparent	No
Metallic colour	No

### Installation, mounting

Fixing type	turn screw lock
Mounting type	flush mounted / surface mounted

### Connection

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Phase pickup	L1
Type of connection	Quickconnect

### Accessories included

With miniature fuse	No
---------------------	----

### Equipment

Number of units	1
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

### Standards

Approvals	NFC 61314
-----------	-----------

### Safety

IK protection code against mechanical impacts	07
Protection	without protective screen

### Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes

### Identification

Range	cubyko
-------	--------