



WNA160

cubyko Schuko Socket composable grey IP55

Technical properties

Architecture

| | |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

Functions

| | |
|-----------------------------------|----|
| Integrated earth fault protection | No |
| Centralized terminal connections | No |
| With orientation lighting | No |
| Overvoltage protection | No |

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Compatibility

| | |
|-------------------------|----|
| IFTTT support available | No |
|-------------------------|----|

Controls and indicators

| | |
|---------------------------|---------|
| Indicator lamp | no |
| With or without indicator | without |

Connectivity

| | |
|--------------------------|----|
| With USB charging socket | No |
|--------------------------|----|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Nominal voltage | 250 V |
| Frequency | 50/60 Hz |

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Dimensions

| | |
|---|---------|
| Depth | 64 mm |
| Installation depth, flush-mounted boxes | 40 mm |
| Depth of installed product | 22.8 mm |
| Height of installed product | 75 mm |
| Width of installed product | 75 mm |
| Height | 75 mm |
| Width | 75 mm |

Capacity

| | |
|--------------------------|---|
| Number of modules for WA | 2 |
|--------------------------|---|

Cover, door

| | |
|---------------|----|
| Interlockable | No |
|---------------|----|

Power supply

| | |
|----------------------|-------------------------|
| Special power supply | No special power supply |
|----------------------|-------------------------|

Materials

| | |
|--------------------|----------------------|
| RAL colour | RAL 7011 - Iron grey |
| Material | Mixed materials |
| Surface appearance | satın finish |
| Transparent | No |
| Metallic colour | No |

Connection

| | |
|-----------------------------|--------------|
| Number of accessible phases | 1 |
| Type of connection | Quickconnect |

Accessories included

| | |
|---------------------|----|
| With miniature fuse | No |
|---------------------|----|

Equipment

| | |
|---------------------------------------|----|
| Number of units | 1 |
| Number of socket outlets switchable | 0 |
| On/Off switch | No |
| With transparent product label holder | No |

Standards

| | |
|-----------|-----------|
| Approvals | NFC 61314 |
|-----------|-----------|

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | 07 |
| Protection index IP | IP55 |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -15...30 °C |
| Storage/transport temperature | -50...50 °C |
| Insulated | Yes |

Identification

| | |
|---------|---|
| Version | F |
|---------|---|